

Approved Tester		Swagelok Company					
Address		29500 Solon Road, Solon, Ohio 44139 USA					
【Approved Range】							
Approval Number	M A B - 4 6 8 - N - II - 1				Equipment Type	Fittings	
Fitting Type	Material		Design Temperature		Design Pressure (MP a)	End Connection Size (A)	Other Comments
	Classification	Group	Highest (°C)	Lowest (°C)			
2-Ring Compressing Type	Stainless Steel	G1	400	-196	75.6 and under	10 and under	Welded Construction Excluded
		G4	800	-269			
		G6	800	-196			
	Corrosion-Resistant, Heat-Resistant Alloys	G2	350	-30	24.6 and under	10 and under	
Metal Gasket Type	Stainless Steel	G1	400	-196	21.6 and under	25 and under	
		G4	800	-269			
		G6	800	-196			
	Corrosion-Resistant, Heat-Resistant Alloys	G2	350	-30	24.6 and under	25 and under	
O-Ring Type	Stainless Steel	G1	400	-196	34.4 and under	25 and under	
		G4	800	-269			
		G6	800	-196			
Others (2-Ring Compressing Taper Metal Touch Type)	Stainless Steel	G1	400	-196	63.8 and under	10 and under	
		G4	800	-269			
		G6	800	-196			